




CIRCUIT: 4PDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4

X.XX=±0.25

- TERM. NOS. FOR REFERENCE ONLY.
- RATING 0.1A @30V DC

▲ 5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE
 HOUSING: PBT UL94HB
 BASE: PA66 UL94HB
 ACTUATOR: POM
 CAP: ABS UL94V0

- CONTACT RESISTANCE: 100 mΩ (INITIAL)

▲ 7. TIMING: NON-SHORTING

- OPERATING FORCE: 280±50GF



- TRAVEL: LATCHING
 2MM TO LOCK
 3MM OVERALL

- ELECTRICAL LIFE: 10000 CYCLES

- OPERATING TEMP: -20°C TO +70°C



- 2002/95/EC (ROHS) COMPLIANT

- ▲ DENOTES CRITICAL PARAMETER.



PBH4UEEKZXNAGX
 ▲ (Q960009)

1SBLK
 Q800310 ▲



E	15942	MOVE KZX 0.45MM CLOSER TO SWITCH	4/4/06	BK
D	15681	ADD CRITICAL TO 2.50 DIM	1/16/06	PH
C	15336	ADDED ROHS NOTE, EDIT PC MOUNT.	9/27/05	PH
B	15260	REVISED CAP DESCRIPTION, NOTE 5	9/8/05	PH
A	15208	RELEASED FOR PRODUCTION	8/26/05	PH
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
 TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE PBH4UEEKZXNAG1SBLK

SCALE 2.5:1

DATE 08/26/05

DR PH

DWG XQ0011P

REV E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PBH4UEEKZXNAG1SBLK](#)