


RECOMMENDED P.C.B. LAYOUT




CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
ON	NONE	ON
2-3	NONE	2-1

() = Momentary

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 3A @ 120 VAC or 28 VDC, 1A @ 250 VAC
- ▲ 5. CONTACTS: SILVER
6. ELECTRIC LIFE: 30,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C



B	21942	UPDATE PRINT	8/4/15	MW
A	--	RELEASED FOR PRODUCTION	--	--
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

					
TITLE <i>200MSP2T1B1M2QE</i>					
SCALE <i>2:1</i>	DATE <i>9/18/98</i>	DR <i>MM</i>	DWG <i>T213005</i>	REV <i>B</i>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[200MSP2T1B1M2QE](#)