



CIRCUIT: 2P, SPST  
CONTACT CONFIGURATION  
ON-OFF (ILLUMINATED)



ACTUATOR: TRANSLUCENT  
GREEN LENS






RECOMMEND PANEL MOUNTING

| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
| ON              | OFF    |
| 2-1             | OPEN   |

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4  
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 12 VDC MAX.
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: -20°C to 85°C
9. LED: 12V GREEN
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT.



|      |         |                                            |          |      |
|------|---------|--------------------------------------------|----------|------|
| B    | 17942   | CHANGE TO TRANSLUCENT GREEN LENS, 3 TERMS. | 1/24/08  | BLR  |
| A    | 16814   | RELEASED FOR PRODUCTION                    | 1/8/2007 | TN   |
| REV. | ECN No. | DESCRIPTION                                | DATE     | CHKD |

|                               |          |     |         |     |
|-------------------------------|----------|-----|---------|-----|
| TITLE                         |          |     |         |     |
| RR3112BBLKGRNGRNEF4 - SPECIAL |          |     |         |     |
| SCALE                         | DATE     | DR  | DWG     | REV |
| 2:1                           | 1/8/2007 | BLR | F130513 | B   |

THE INFORMATION CONTAINED IN THIS DOCUMENT  
IS PROPRIETARY TO E-SWITCH AND IS  
NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[RR3112BBLKGRNGRNEF4](#)