



PANEL THICKNESS	X dimension
0.75-1.25 [.030-.049]	19.2-0.1 [.756]
1.25-2.0 [.049-.079]	19.4-0.1 [.764]
2.0-3.0 [.079-.118]	19.8-0.1 [.780]



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
<ON>	OFF	<ON>
1-1a	OPEN	1-1b





< >=MOMENTARY



CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- RATING: 15A @ 125VAC OR
6A @ 250VAC
APPROVALS: UL, CSA, NEMKO, FEMKO, DEMKO, SEMKO
- MATERIALS: TERMINALS: SILVER PLATED COPPER ALLOY
CONTACTS: COIN SILVER, SILVER PLATED
- ELECTRIC LIFE: 10,000 CYCLES
- CONTACT RESISTANCE: <20 MEGA-OHM
- INSULATION RESISTANCE: >1000 MEGA-OHM
- DIELECTRIC STRENGTH: >1500 V 1 MINUTE
>3000 V BETWEEN POLES
- ▲ DENOTES CRITICAL PARAMETER.

**E-SWITCH®**

TITLE

R1966IWHTWHTBF

SCALE

1.5:1

DATE

9/16/03

DR

AR

DWG

M306216

REV

A

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

A	13453	RELEASED FOR PRODUCTION	9/16/03	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R1966IWHTWHTBF](#)