




CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
DN	OFF	DN
2-3	OPEN	2-1



RECOMMEND P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0 ± 0.4
 0.00 ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A, @120VAC or 28VDC; 2A, @250VAC.
5. ELECTRICAL LIFE: 50,000 make-and-break cycles
at full load.
6. INSULATION RESISTANCE: 1,000M ohm min.
7. DIELECTRIC STRENGTH: 1,000V RMS @sea level.
8. OPERATING TEMP.: -30°C to 85°C .

7. DIELECTRIC STRENGTH: 1,000V RMS @sed level.			
8. OPERATING TEMP.: -30°C to 85°C.			
A	10364	RELEASED FOR PRODUCTION	
REV.	ECN NO.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TITLE			
100 SP-3 T2 B4 M6 Q E			
SCALE	DATE	DR	DWG
2:1	9/21/99	MM	T113039
			REV
			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[100SP3T2B4M6QE](#)