


▲ SWITCH FUNCTION




POS. 1	POS. 2
OFF	ON
OPEN	1-3, 2



CIRCUIT: SPST

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = 0.4
X.XX = 0.25
3. TERMINAL NO'S FOR REFERENCE ONLY.
- ▲ 4. CONTACT RATINGS:
16A 125VAC [UL, cUL]
3/4HP 250VAC [UL, cUL]
16(6)A 250V~ 1E4 T125 [VDE]
10(4)A 250V~ 5E4 T125 [VDE]
5. CONTACT RESISTANCE: 35mΩ MAX. INITIAL @ 50VAC
6. INSULATION RESISTANCE: 100MΩ @ 500VDC
7. DIELECTRIC STRENGTH: 1500VAC FOR 1 MINUTE
8. ELERTICAL LIFE: 6,000 CYCLES [UR, cUR]
10,000 CYCLES [VDE]
50,000 CYCLES [VDE]
9. ▲ DENOTE CRITICAL PARAMETER
10. 2011/65/EU (ROHS) COMPLIANT
- ▲ 11. ILLUMINATION VOLTAGE: 12V
12. LENS COLOR: GREEN



TITLE PR141C4000-134 (Gray Body)

A	23419	RELEASE TO PRODUCTION	6/27/18	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1:1	DATE 6/27/2018	DR MW	DWG 38-PR141C4000134	REV A
--------------	-------------------	----------	-------------------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PR141C4000-134](#)