





RECOMMENDED P.C.B. LAYOUT






CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
<DN>	DIFF	<DN>	
2-3	DPEN	2-1	

NOTES: ()=Momentary

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 28VDC:
2A @250VAC
5. FIXED TERM. MOVING CONTACT:
6. ELECTRICAL LIFE: 40,000 make-and-break cycle
at full load.
Copper Alloy w/Silver plating
7. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
8. OPERATING TEMP.: -30°C to 85°C
9. ▲ DESIGNATE MAJOR FEATURE:
10. 2002/95/EC (ROHS) COMPLIANT



D	17292	FIXED ACT DIM AND NOTE 10.6	5/15/07	TN
C	14267	CORRECTED RATINGS	8/26/04	CJB
B	11520	REVISED AND REDRAWN	5/3/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE		SCALE	DATE	DR	DWG	REV
100SP4T1B4M6QE		2:1	5/15/07	TN	T114023	D



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[100SP4T1B4M6QE](#)