


# SERIES KC 1901 SWITCHES

## ROTARY SWITCHES



E-SWITCH®



### SPECIFICATIONS

Rating:	100 mA @ 16 VDC
Life Expectancy:	10,000 cycles typical
Contact Resistance:	50 mΩ initial @ 2-4 VDC, 100mA
Dielectric Strength:	1,000 max V rms at sea level
Insulation Resistance:	100 MΩ min.
Operating Force:	0.5 N/cm

### MATERIALS

Cover:	Stainless steel
Contact:	Silver-plated copper alloy
Terminals:	Silver-plated copper alloy

### FEATURES & BENEFITS

- ▶ 9-position rotary
- ▶ Thru-hole termination
- ▶ Positive detents

### APPLICATIONS/MARKETS

- ▶ Industrial controls
- ▶ Test & instrumentation
- ▶ Appliance
- ▶ HVAC



### HOW TO ORDER

SERIES	MODEL NO.	ACTUATOR LENGTH
KC	1901	A = 9.8mm







Example Ordering Number  
KC-1901-A

Specifications subject to change without notice.

KC

1901



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC1901A](#)