



NOTES:


1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. CONTACT MATERIAL:
STANDARD SILVER over COPPER ALLOY
7. OPERATING FORCE: 425 ± 100 CM/STANDARD
8. OPERATING TEMP: -30° to 85°C
9. CIRCUIT SP: 12 POSITIONS, 30° INDEX, NO STOPS
10. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
11. DESIGNATE MAJOR DIMENSIONS
12. HARDWARE SUPPLIED ON SWITCH - SEE BELOW
STOP RING, LOCKWASHER, & LOCKRING




CONTACT CONFIGURATION
Timing: NON-SHORTING (BBM)



RECOMMENDED P.C.B. LAYOUT



HARDWARE SUPPLIED
ON SWITCH



E-SWITCH®				TITLE			
B	12871	REV DESC/ PER NEW CATALOG	CJB	3/4/03	SCALE	DATE	DR
A	12064	RELEASED FOR PRODUCTION	CJB	4/15/02	1.5:1	4/15/02	CJB
REV.	ECN No.	DESCRIPTION	CHKD	DATE			DWG
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND ITS NOT TO BE COPIED OR TRANSFERRED				KC-19-A (30.0mm)-01-N-P-S			
				G510100			
				REV B			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC19A30.001NPS](#)