





NOTES:

1. ALL DIMENSIONS IN MM[INCH]

2. GENERAL TOLERANCE: $x.x = \pm 0.4$ $x.xx = \pm 0.25$

3. TERM. NOS. FOR REFERENCE ONLY.

▲ 4. RATING: 1A @125VAC, 0.5A @250VAC

5. CONTACT RESISTANCE: 10milli-OHMS

6. DIELECTRIC STRENGTH: 1000 VAC-1Minute

7. MATERIALS:

HOUSING: ZINC ALLOY W/CHROME PLATING

CYLINDER: ZINC ALLOY W/CHROME PLATING


▲ TERMINAL AND CONTACTS: SILVER PLATED

▲ KEYS (2) KEY CODE 1501: ZINC ALLOY, CHROME PLATING


8. DENOTES CRITICAL PARAMETER.

9. 2002/95/EC (ROHS) COMPLIANT

▲ 10. KEYLOCK, KEYS, AND HEX NUT TO BE PACKED TOGETHER IN INDIVIDUAL BAGS.



RECOMENDED PANEL CUTOUT

CIRCUIT: SPDT
CONTACT CONFIGURATION

45° INDEXING

SWITCH FUNCTION		
POS 1	POS 2	POS 3
OFF	ON 1-2	ON 3-4

LEGEND

● = INDICATES KEY PULL POSSIBLE

● = DETENT POSITION



TITLE KO132C1501

C	17991	REDRAWN AND ADD NOTE 10	3/3/08	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1

DATE 3/3/2008

DR RC

DWG K400104

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KO132C1501](#)