





NOTES:


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING: 20VDC @ 1mA
4. CONTACT RESISTANCE: 200Ω MAX.
5. INSULATION RESISTANCE: 100MΩ MIN. @ 100VDC.
- ▲ 6. OPERATING FORCE: 125± 35gf
7. TRAVEL: 1.3 +/- 0.3 mm
8. OPERATING TEMPERATURE: -40°C TO 85°C
9. OPERATING LIFE: 1,000,000 CYCLES
- ▲ 10. LED: BLUE
11. ▲ DENOTES CRITICAL PARAMETERS
12. CONTACT MATR'L: GOLD FLASH OVER NICKEL



▲ WHITE CAP
with
BLUE LED



ALIGNMENT
POST



LED SPECS	UNITS	BLUE
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	3.3 TYP 4.0 MAX.
LUMINOUS INTENSITY @ 20mA	mcd	240 TYP

REV	ECO NO	DESCRIPTION	DATE	BY
D	ECO-101243	UPDATE TO CURRENT LED SPECS	09/22/22	JS

 E-SWITCH®				OBJECT ID	
				000006812	
TITLE LP15R1WHTBLU-N					
SCALE	DATE	DR	DWG	REV	
2:1	3/1/2010	BLR	B270004	D	

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP15R1WHTBLU-N](#)