





P.C. MOUNTING







CIRCUIT: SPDT

O.P. (MM)	P.T. (MM)
10.8±0.8	3.60 MAX

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
- ▲ 3. RATING: 0.1A @ 5 VDC
0.1A @ 125VAC UL
- ▲ 4. OPERATING FORCE: 35 ± 10 gf
5. OPERATING TEMP: -25°C TO 75°C
6. CONTACT RESISTANCE: 100mΩ MAX. INITIAL
7. ELECTRICAL LIFE: 10,000 CYCLES MIN.
8. MECHANICAL LIFE: 1,000,000 CYCLES MIN.
9. INSULATION RESISTANCE: 100 MΩ MIN. @ 500V
10. DIELECTRIC STRENGTH: 1,500VAC - 1 MINUTE
11. ▲ DENOTES CRITICAL PARAMETER.
12. PACKAGED IN TRAYS, 120 PIECES PER TRAY.
13. 2002/95/EC (ROHS) COMPLIANT



A	20344	RELEASE FOR PRODUCTION	12/16/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

				
TITLE SS075Q102F035V1A				
SCALE 4:1	DATE 12/16/2011	DR BGL	DWG Q971032	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[SS075Q102F035V1A](#)