



SCHEMATIC ▲

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 20VDC, 100mA MAX; SPST
5. CONTACT RESISTANCE: 150 MILLI-OHM MAX.
6. INSULATION RESISTANCE: 10MEGA-OHM MIN @500VDC.
7. DIELECTRIC STRENGTH: 500VAC FOR 1 MINUTE
8. OPERATING FORCE: 250± x50GF
9. OPERATING LIFE: 50,000,000 CYCLES
10. OPERATING TEMP: -5°C TO +60°C
11. STORAGE TEMPERATURE: -40°C TO +90°C
12. TOTAL TRAVEL: 3.30mm±0.3
- ▲13. TRAVEL TO ELECTRICAL MAKE: 2.9 ±0.5MM
- ▲14. LED COLOR: RED
15. 2002/95/EC (ROHS) COMPLIANT
16. ▲ DENOTES CRITICAL PARAMETER.

CLEAR CAP WITH
WHITE DIFFUSER

▲ LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	1.95 Typ-2.5 Max
LUMINOUS INTENSITY @ 10mA	mcd	280 Typ



B	19592	CHANGE DIMS	1/17/11	BGL
A	19259	New Release	8/20/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP16OA1BSTWR

SCALE 2:1

DATE 7/30/2010

DR rc

DWG B160004

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP16OA1BSTWR](#)