




▲ **CIRCUIT: SPST**  
**OFF (ON)**

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. RATING: 20VDC @ 1mA or 5VDC @ 5mA
4. CONTACT RESISTANCE: 200 $\Omega$  MAX. @ 5VDC, 1mA
5. INSULATION RESISTANCE: 100M $\Omega$  MIN. @ 100VDC.
- ▲ 6. OPERATING FORCE: 125  $\pm$  35gf
7. TRAVEL: 1.3  $\pm$  0.3 mm
8. OPERATING TEMPERATURE: -40°C to 85°C
9. OPERATING LIFE: 300,000 CYCLES
- ▲ 10. LED: WHITE
11. ▲ DENOTES CRITICAL PARAMETERS
12. 2011/65/EU (ROHS) COMPLIANT



▲ **WHITE CAP**  
**with**  
**WHITE LED**



▲ LED SPECS	UNITS	WHITE	
FORWARD CURRENT	mA	20	
FORWARD VOLTAGE @ 20mA	VDC	2.8 MIN.	4.0 MAX.
LUMINOUS INTENSITY @ 20mA	mcd	400 TYP.	



E-SWITCH®

A	22990	New Release	9/13/17	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP2S2WHTWHT-N

SCALE	DATE	DR	DWG	REV
2:1	9/12/2017	MW	B250014	A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP2S2WHTWHT-N](#)