







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: CURRENT: .01mA-250mA
VOLTAGE: 20mV-50 VDC
5. OPERATING LIFE: 30,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 1000VDC, 1,000 Mega-OHMS MIN.
- ▲ 7. OPERATING FORCE: 250gf ± 100 GRAMS
8. OPERATING TEMP.: -30°C to 85°C (B)
- ▲ 9. TRAVEL: MOMENTARY
FULL TRAVEL 5.1 ± 0.5mm
10. CONTACT RESISTANCE: 50 Milli-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT
- ▲ 13. LED COLOR: YELLOW



ISOMETRIC



▲ LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	2.1 TYP-2.6 MAX
LUMINOUS INTENSITY @ 20mA	MCD	30



B	19585	CHANGE DIMS & TEMP.	1/14/11	BGL
A	19040	Release For Production	5/5/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP370ACGY

SCALE 2=1

DATE 5/5/2010

DR BLR

DWG T010002

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP37OACGY](#)