








NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REFERENCE ONLY.
- RATING: 12VDC, 12mA; SPST
- CONTACT MATERIAL: GOLD
- CONTACT RESISTANCE: 50 MILLI-OHM MAX.
- INSULATION RESISTANCE: 500VDC, 100 MEGA-OHM MIN.
- OPERATING FORCE: 150±100GF
- OPERATING LIFE: 200,000 CYCLES
- OPERATING TEMP: -20°C TO +70°C
- LED COLORS: BLUE (BOTH)
- TRAVEL: 2.20mm±0.20
- 2002/95/EC (ROHS) COMPLIANT
- ▲ DENOTES CRITICAL PARAMETER.



▲ LED SPECS	UNITS	BLUE
FORWARD CURRENT	mA	25
FORWARD VOLTAGE @20mA	VDC	3.3
LUMINOUS INTENSITY @ 10mA	mcd	585



E-SWITCH™

A	18339	RELEASE FOR PRODUCTION	12/15/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP60A1ASBB

SCALE 2=1

DATE 12/15/2008

DR BLR

DWG B220005

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP6OA1ASBB](#)