








- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. RATING: 12VDC, 12mA; SPST
 5. CONTACT MATERIAL: GOLD
 6. CONTACT RESISTANCE: 50 MILLI-OHM MAX.
 7. INSULATION RESISTANCE: 500VDC, 100 MEGA-OHM MIN.
 - ▲ 8. OPERATING FORCE: 150 ± 100 GF
 9. OPERATING LIFE: 200,000 CYCLES
 10. OPERATING TEMP: -20°C TO +70°C
 - ▲ 11. LED COLORS: GREEN, GREEN
 12. TRAVEL: $2.20\text{mm} \pm 0.20$
 13. 2002/95/EC (ROHS) COMPLIANT
 14. ▲ DENOTES CRITICAL PARAMETER.

▲ LED SPECS	UNITS	GREEN	GREEN
FORWARD CURRENT	mA	25	25
FORWARD VOLTAGE @20mA	VDC	2.0	2.0
LUMINOUS INTENSITY @ 10mA	mcd	412	412



A	20375	New Release	01/03/12	BMA
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP6OA1ASGG				
SCALE 2=1	DATE 1/3/2012	DR BMA	DWG B220010	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP60A1ASGG](#)