









PANEL MOUNTING



CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A@250VAC UL, VDE 8A@125VAC UL, VDE
6A @24VDC, 0.2A @24VDC
5. MECHANICAL LIFE: 2,000,000 OPERATIONS
6. DEGREE OF PROTECTION: IP40
7. PANEL THICKNESS: 0.5 - 5.0 mm
- ▲ 8. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
9. TRAVEL: 3.0mm FULL, 2.0mm LATCH
10. OPERATING TEMP.: -25°C to 55°C
11. LAMP VOLTAGE: 110 VAC GREEN NEON
12. ▲ DENOTES CRITICAL PARAMETER.



PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040020	D16EES12
2	1	F050411	50-004-41 110VAC GREEN NEON
3	1	F050305	50-003-05 TRANSPARENT WHITE CONCAVE



E-SWITCH®



TITLE D16EES12FGRNWHT

A	19217	RELEASED FOR PRODUCTION	7/23/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5:1

DATE 7/23/2010

DR BLR

DWG XF0826P

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16EES12FGRNWHT](#)