



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 3A @120V or 28VDC;
1A @250VAC
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy w/SILVER plate.
6. CONTACT RESISTANCE:
10mILL-Ohms initial @2-4VDC.
7. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
8. INSULATION RESISTANCE: 1,000M ohm min.
9. DIELECTRIC STRENGTH: 1000V RMS @sea level
10. OPERATING TEMP.: -30°C to 85°C



SWITCH FUNCTION	
DN	(DN)
2-1	2-3

() =MDMENTARY



RECOMMENDED P.C.B. LAYOUT

TITLE			
800 SP-8 B7 M7 Q E /C1 BLK			
E-SWITCH®			
REV.	ECN No.	RELEASED FOR PRODUCTION	DESCRIPTION
A	11607	6/18/02	CJB
DATE	DATE	CHKD	SCALE
6/18/02	6/18/02	CJB	2:1
DR	DATE	DATE	DATE
CJB	6/18/02	6/18/02	6/18/02
DWG	XT0098P	XT0098P	XT0098P
REV	A	A	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[800SP8B7M7QEC1BLK](#)