




PANEL CUTOUT


PANEL THICKNESS	(x)
0.75 - 1.25	30.0
1.25 - 2.00	30.2
2.00 - 3.00	30.5

CIRCUIT: DPST
OFF - ON

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	2-1, 5-4

NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. CONTACT RATINGS: 16A @ 125/250VAC [cURus]
20A @ 125/250VAC [cURus]
1/3HP 125/250VAC T105 [cURus]
3/4HP 125/250VAC T105 [cURus]
16(8)A 250V~ 1E4 T125 [VDE, ENEC]
10(2)A 250V~ 5E4 [VDE, ENEC]
16(4)A 250V~ 1E4 T85/55 [VDE, ENEC]
6. CONTACT RESISTANCE: 20mΩ MAX. INITIAL
7. INSULATION RESISTANCE: 100MΩ MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [cURus]
10. OPERATING TEMPERATURE: -20°C TO 55°C [cURus]
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT
- ▲ 13. ILLUMINATION: NON-ILLUMINATED

BODY COLOR:
BLACK

TITLE RB242D1821

A	21728	RELEASE FOR PRODUCTION	11/26/14	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1:1	DATE 11/26/2014	DR rc	DWG 14-RB242D1821	REV A
--------------	--------------------	----------	----------------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RB242D1821](#)