




| O.P. (MM) | P.T. (MM) |
|-----------|-----------|
| 9.5 ±0.8  | 4.2 Max.  |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4  
X.XX = ± 0.25
3. RATING: 5A @125/250VAC UL, CUL APPROVED
- ▲ 4. OPERATING FORCE: 25 ± 12gf
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MΩ
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER

| REV | ECO NO     | DESCRIPTION                | DATE     | BY | E-SWITCH®              |           |    |         | OBJECT ID |
|-----|------------|----------------------------|----------|----|------------------------|-----------|----|---------|-----------|
| C   | ECO-100799 | REMOVE VDE RATING AND LOGO | 03/24/22 | JS | TITLE MS0850503F025C1C |           |    |         | 000021291 |
|     |            |                            |          |    | SCALE                  | DATE      | DR | DWG     | REV       |
|     |            |                            |          |    | 2:1                    | 6/23/2016 | MW | Q970156 | C         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[MS0850503F025C1C](#)