










P.C. LAYOUT

▲ SCHEMATIC
N.O.

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. RATING: 1mA @ 5VDC
- ▲ 5. OPERATING POINT = 2.20 mm
- ▲ 6. OPERATING FORCE: ≤ 50 gf
7. CONTACT RESISTANCE: 2 OHMS MAX. (INITIAL)
8. ELECTRICAL LIFE: 100,000 min.
9. INSULATION RESISTANCE: 100 MOHMS MIN @ 100VDC
10. OPERATING TEMPERATURE: -10°C to 80°C
11. DIELECTRIC STRENGTH: 100 VAC FOR 1 MINUTE.
12. PACKAGING: 2,600 PER REEL
13. ▲ DENOTES CRITICAL PARAMETER

DETAIL A
SCALE 10 : 1

C	24378	update Oper. Temp. to -10C to 80C	7/1/20	MW
B	23162	Update print	1/11/18	MW
A	21286	New Release	10/28/13	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE TD4700BQ

SCALE
5:1DATE
9/27/2013DR
rcDWG
N470001REV
C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TD4700BQ](#)