






RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 0.7 ~ 2.5mm

SWITCH FUNCTION	
POS. 1	POS. 2
OPEN	1-3, 2-4



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.5
X.XX = ± 0.30
- TERMINAL NUMBERS FOR REF. ONLY
- RATING: 16(16)A @ 127VAC
- ILLUMINATION VOLTAGE: 127VAC
- CONTACT RESISTANCE: 50m Ω MAX.
- INSULATION RESISTANCE: 2M Ω @ 500VDC
- DIELECTRIC STRENGTH: 1,300VAC MIN. FOR 1 MINUTE
- ELECTRICAL LIFE: 50,000 CYCLES
- OPERATING TEMPERATURE: 0°C to 55°C
- ACTUATION FORCE: 13 \pm 5N (AT 5mm TRAVEL)
- INGRESS PROTECTION: IP66 (AFTER MOUNTING)
- ▲ DENOTES CRITICAL PARAMETER
- 2011/65/EU (ROHS) COMPLIANT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-101925	PRINT UPDATE	05/30/23	JS					100123364
A	ECO-101536	NEW RELEASE	01/12/23	MR	TITLE PB66EE2CR6P31				
					SCALE 1:1	DATE 12/27/2022	DR MJR	DWG 34-PB66EE2CR6P31	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PB66EE2CR6P31](#)