


SCHEMATIC



SPECIFICATIONS

FUNCTION:
2P1T OFF-ON

RATINGS:
ANSI/UL 1054 and CAN/CSA C22.2 No. 55 (E194579):
16A 125VAC [cURus]
8A 250VAC [cURus]

DIN 61058-1/VDE 0630-1:1993-05 (40017071):
16(4)A 250V~ 1E4 T125/55 [VDE]
16(8)A 250V~ 1E4 T125/55 [VDE]

ILLUMINATION VOLTAGE:
250V

CONTACT RESISTANCE:
Initial: 35mΩ Max. at 500VAC

INSULATION RESISTANCE:
100MΩ Min. at 500VDC

DIELECTRIC STRENGTH:
1,500VAC For 1 Minute

ELECTRICAL LIFE:
6,000 Cycles [cURus]
10,000 Cycles [VDE]

TEMPERATURE:
-20°C to 85°C [cURus]
-20°C to 125°C [VDE]

APPROVALS:



COLORS AND MARKINGS

BODY:
Black

ACTUATOR:
Black

LENS:
Transparent Green

MARKING:
None

MARKING COLOR:
None

MATERIALS

BODY:
Polyamide 6/6 (PA66), UL94 V-2

ACTUATOR:
Polyamide 6/6 (PA66), UL94 V-2



LENS:
Polycarbonate (PC) UL94 V-2

SPRING:
Piano Wire


LAMP:
Neon Bulb

CONTACTS:
Silver Alloy Clad Copper

TERMINALS:
Silver Plated Copper
Silver Plated Brass



SUGGESTED PANEL CUTOUT




PANEL THICKNESS	X
0.030~0.049 [0.75~1.25]	1.181 [30.0]
0.049~0.079 [1.25~2.00]	1.189 [30.2]
0.079~0.118 [2.00~3.00]	1.200 [30.5]

ACTUATOR	A	09/09/09	CAB
BODY	A	09/08/26	CAB
COLORS	A	09/08/26	CAB
MATERIALS	A	09/09/09	CAB
SPECIFICATIONS	A	09/08/26	CAB
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

C	CHANGED VDE APPROVAL TO SEMKO APPROVAL	18892	11/05/04	CAB
B	CORRECTED BULB TYPE	PCRD0241	09/12/09	CAB
A	INITIAL RELEASE	PCRD0078	09/10/08	CAB
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.008 [±0.2] / ±1°
SCALE	DRAWING NOT TO SCALE



RB242C1100-237

ITEM NUMBER	DATE	REVISION
38-RB242C1100237	MAY 4, 2011	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RB242C1100-237](#)