


PV4 SERIES ANTI-VANDAL SWITCH

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS



Audio / Visual



Security Devices



Industrial Controls



Kiosks



Electrical Housewares



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 2A, 24VDC
Electrical Life: 50,000 Cycles
Contact Resistance: 50mΩ Max.
Insulation Resistance: 1000 MΩ Min.
Dielectric Strength: 2,000VAC
Operating/Storage Temperature: -20°C to 55°C
Travel: 2.50mm
Moisture Protection: IP65
Contact Arrangement: SPDT, DPDT
Actuation Force: 4 N
Panel Thickness: 1-11mm
Mounting Nut Torque: 5-14Nm

FEATURES & BENEFITS

- 19mm diameter panel cutout
- RGB LED option
- Dot, ring or power symbol illumination available
- Multiple function options
- IP65 rated
- SPDT & DPDT

PART NUMBER CONFIGURATOR

Series	Actuator Options	Terminal Options	Function Options	Rating Options	Body Finish Options	Actuator Finish Options	Contact Material Options	Lens Style Options	LED-Color Options	Illumination Voltage Options	Graphic (Optional)
PV4	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐
	F - Flat H - High	2 - Solder 6 - Screw*	3 - 1P On - On B - 1P On - (On) G - 2P On - On H - 2P On - (On) Y - Double break 1P Off - (On) 1P On - (Off)	0 - 2A, 24VDC	S - Stainless Steel 1 - Black Anodized	S - Stainless Steel 1 - Black Anodized	None - Silver G - Gold	NONE - Non-Illuminated 2 - Dot Illumination 3 - Ring Illumination	NONE - Non-Illuminated 0 - White 1 - Red 2 - Orange 3 - Green 4 - Blue 5 - Yellow F - Red/Orange G - Red/Green H - Red/Blue J - Red/Yellow K - Orange/Green L - Orange/Blue M - Orange/Yellow R - RGB LED***	NONE - Non-Illuminated 1 - Base Voltage 3 - 6V 4 - 12V 5 - 24V 6 - 125V 7 - 250V	M01 - Power symbol laser etched M26 - Power symbol illuminated**

NOTES:

() denotes function is momentary

* Screw termination is available only with "Y" function option

** Illuminated power symbol graphic is only available with ring illumination

*** RGB is only for SPDT functions 3 and B

Specifications subject to change without notice



E-SWITCH®


www.e-switch.com

800.867.2717

2


PV4 SERIES ANTI-VANDAL SWITCH

STANDARD LED FUNCTIONS 3, B, G & H




Notes:


Functions 3 & B are SPDT
Functions G & H are DPDT




**SPDT LED
SCHEMATIC**





**SPDT Non ILL.
SCHEMATIC**



**DPDT LED
SCHEMATIC**



**DPDT Non ILL.
SCHEMATIC**



E-SWITCH®

www.e-switch.com



800.867.2717

3


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

PV4 SERIES ANTI-VANDAL SWITCH


Y FUNCTION W/ SCREW TERMINALS




**SCHEMATIC
STD LED**



**SCHEMATIC
Non-ILLUM.**



PANEL CUTOUT



POWER SYMBOL PANEL CUTOUT








E-SWITCH®

www.e-switch.com

800.867.2717





PV4 SERIES ANTI-VANDAL SWITCH

Y FUNCTION W/ SOLDER TERMINALS



PV4 SERIES ANTI-VANDAL SWITCH

RGB LENS COLOR FUNCTIONS 3 & B



E-SWITCH®


www.e-switch.com

800.867.2717


6

PV4 SERIES ANTI-VANDAL SWITCH


LENS / ACTUATOR OPTIONS





NON-ILLUMINATED



DOT ILLUMINATED





RING ILLUMINATED





GRAPHIC OPTIONS

M01 GRAPHIC



M26 GRAPHIC



E-SWITCH®

www.e-switch.com

800.867.2717

7

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PV4F2B0SS-331](#) [PV4F2B0SS-341](#) [PV4F2B0SS-311](#) [PV4F2B0SS-334](#) [PV4F2G0SS-325](#) [PV4F2G0SS-331](#)
[PV4F2H011](#) [PV4F2H0SS-344](#) [PV4F2Y011-345](#) [PV4F2Y0SS-3G5](#) [PV4F6Y0SS-335](#) [PV4F2H011-341](#) [PV4F2Y011-](#)
[311](#) [PV4F2G011-311](#) [PV4F2Y0SS-341](#) [PV4F2H011-311](#) [PV4F2G011-341](#) [PV4F2Y011-341](#) [PV4F2H0SS-341](#)
[PV4F2G0SS-341](#) [PV4F230SS](#) [PV4F230SS-314](#) [PV4F230SS-315](#) [PV4F230SS-324](#) [PV4F230SS-325](#) [PV4F230SS-](#)
[331](#) [PV4F230SS-335](#) [PV4F230SS-346](#) [PV4F2G0SS](#) [PV4F2G0SS-314](#) [PV4F2G0SS-334](#) [PV4F2G0SS-344](#)
[PV4F2G0SS-354](#) [PV4F2H0SS-345-M01](#) [PV4F2Y0SS](#) [PV4F2Y0SS-201](#) [PV4F2Y0SS-211](#) [PV4F2Y0SS-214](#)
[PV4F2Y0SS-215](#) [PV4F2Y0SS-216](#) [PV4F2Y0SS-234](#) [PV4F2Y0SS-235](#) [PV4F2Y0SS-241](#) [PV4F2Y0SS-244](#)
[PV4F2Y0SS-245](#) [PV4F2Y0SS-301](#) [PV4F2Y0SS-304](#) [PV4F2Y0SS-311](#) [PV4F2Y0SS-314](#) [PV4F2Y0SS-315](#)
[PV4F2Y0SS-316](#) [PV4F2Y0SS-324](#) [PV4F2Y0SS-325](#) [PV4F2Y0SS-334](#) [PV4F2Y0SS-335](#) [PV4F2Y0SS-344](#)
[PV4F2Y0SS-346](#) [PV4K2T0S9](#) [PV4F23011-334](#) [PV4F2Y011-351](#) [PV4F2B0SS-304](#) [PV4F2Y01S-344](#) [PV4F6Y0SS-](#)
[341](#) [PV4F2Y01S-314](#) [PV4F2Y011-344](#) [PV4F2Y011-314](#) [PV4F23011](#) [PV4F23011-344](#) [PV4F2Y01S-343](#)
[PV4DS2B0SSG](#) [PV4F2B0SS-344](#) [PV4F2G0SS-335](#) [PV4F23011-341](#) [PV4F2H0SS](#) [PV4F2Y0SS-355](#) [PV4F2B0SS-](#)
[345](#) [PV4F2G0SS-311](#) [PV4F2H0SS-351](#) [PV4F2H0SS-315](#) [PV4F2B011-344](#) [PV4F2G011](#) [PV4F2B0SS-343](#)
[PV4F2B0SS-315](#) [PV4F2Y0SS-335](#) [PV4F23011-314](#) [PV4F230SS-334](#) [PV4F2Y0SS-345](#) [PV4F2B011-324](#)
[PV4F230SS-M05](#) [PV4F23011-324](#) [PV4F2B0SS-335](#) [PV4F2Y0SS-331](#) [PV4F230SS-341](#) [PV4F2B011-314](#)
[PV4F230SS-345](#) [PV4F2H0SSG](#)