


▲ SWITCH FUNCTION






POS. 1	POS. 2
ON	(ON)
1-3	1-2

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 M Ω MIN.
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 55°C
- TRAVEL: 2.8mm
- ▲ DENOTES CRITICAL PARAMETER
- LAMP VOLTAGE: 2.8V @ 20mA
- INGRESS PROTECTION: IP65
- HARDWARE SUPPLIED: O-RING AND HEXNUT

▲ RING ILLUMINATION
COLOR: GREEN▲ FLAT ACTUATOR
STAINLESS STEEL▲ LASER ETCHED M01 MARKING
NON-ILLUMINATED POWER SYMBOL▲ BODY
STAINLESS STEELTerminal Orientation shown is for Reference Only.
Orientation may vary in respect to the Flat on the Housing.

D	22347	Update Print, add Terminal Orientation note	6/9/16	MW
C	21350	CHANGE FLAT SIZE ON BODY AND CUTOUT	1/13/14	EBP
B	21333	CORRECT POWER SYMBOL DIAMETER	12/30/13	EBP
A	21261	RELEASE FOR PRODUCTION	10/8/13	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV4F2B0SS-331-M01

SCALE 3:2

DATE 10/8/2013

DR EBP

DWG 52-PV4F2B0SS331M01

REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV4F2B0SS-331-M01](#)