


O.P. (MM)	P.T. (MM)
14.7 ± 0.5	2.0 MAX.




O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPST
NORMALLY OPEN

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 15A @125/250VAC UL, CUL, VDE APPROVED
- ▲ 4. OPERATING FORCE: 160 ± 60 GRAMS
5. OPERATING TEMP: -25~C to 85~C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.



E	24268	update print	4/17/20	MW
D	16897	FIXED OPERATING FORCE NOTE	1/19/2007	TN
C	16007	UPDATE CIRCUIT LAYOUT	5/4/06	CT
B	15632	CHANGES NOTED	12/21/05	PH
A	15261	RELEASED FOR PRODUCTION	9/12/05	PH
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE LS0851500F160C2B

SCALE 1.5:1	DATE 1/19/2007	DR TN	DWG Q950019	REV E
----------------	-------------------	----------	----------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LS0851500F160C2B](#)