



Ø19.00
[.748 in]



PANEL CUTOUT
MAX. PANEL THICKNESS
11.0mm [.433]

SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON
1-3, 4-6	1-2, 4-5




▲ DPDT
CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN mm [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
- ▲ 11. TRAVEL: 2.8mm
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 12V
14. INGRESS PROTECTION: IP65
15. HARDWARE SUPPLIED: O-RING AND HEXNUT
- ▲ 16. ILLUMINATION COLOR: RED

Ø22.00
[.866 in]
Ø13.60
[.535 in]





Ø15.80
[.622 in]

▲ RING
ILLUMINATION

▲ ACTUATOR FINISH
MACHINED STAINLESS



▲ FLAT ACTUATOR
▲ BODY FINISH
MACHINED STAINLESS



▲ NOTE 15
HARDWARE SUPPLIED
M19x1.0



E-SWITCH®

B	23602	UPDATED RATING TO 2A @ 24VDC	10/10/18	MJR
A	21230	INITIAL RELEASE	9/11/13	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV4F2G0SS-314

SCALE
3:2

DATE
9/11/2013

DR
EBP

DWG
52-PV4F2G0SS314

REV
B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV4F2G0SS-314](#)