


SCHEMATIC

ON - (ON) - DPDT ILLUMINATED
() DENOTES MOMENTARY FUNCTION






RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 11.0 [.43 in]

NOTES:

1. DIMENSIONS IN MM [INCH]
2. ALL MATERIAL SHALL BE ROHS COMPLIANT
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
- ▲ 6. LAMP VOLTAGE: RED-1.8V, GREEN-2.8V, BLUE-2.8V
7. INGRESS PROTECTION: IP67
8. TRAVEL: 2.8mm
9. OPERATING TEMP.: -25°C to 55°C
10. INSULATION RESISTANCE: 1,000 MΩ MIN.
11. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
12. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
13. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
14. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 15. SUPPLIED HARDWARE: O-RING AND HEXNUT
16. USE PART NUMBERS DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS.

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 24AWG AWM UL1015, ORANGE	300.0 [11.8 in]
SW1-2	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3	WIRE, 24AWG AWM UL1015, YELLOW	300.0 [11.8 in]
SW1-RED (+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]
SW1-GREEN (+)	WIRE, 24AWG AWM UL1015, GREEN	300.0 [11.8 in]
SW1-BLUE (+)	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]



E-SWITCH®

B	23993	UPDATED NOTES	8/13/19	MJR
A	23944	NEW RELEASE	6/20/19	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV4FWB011-3R1

SCALE

2:3

DATE

6/20/2019

DR

MJR

DWG

52-PV4FWB0113R1

REV

B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV4FWB011-3R1](#)