






▲ LED COLOR: RGB
RED/GREEN/BLUE



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REFERENCE ONLY.
4. RATING: 12VDC, 100mA
5. CONTACT MATERIAL: GOLD PLATED
6. CONTACT RESISTANCE: 200 m Ω MAX.
7. INSULATION RESISTANCE: 500VDC, 100 M Ω MIN.
8. OPERATING FORCE: 200 $\pm$ 80gf
9. MECHANICAL LIFE: 2,000,000 CYCLES
10. OPERATING TEMP: -40°C to +85°C
- ▲ 11. LED COLORS: RED / GREEN / BLUE
12. TRAVEL: 4.50mm $\pm$ 0.20mm
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. SWITCH HAS TACTILE FEEDBACK WHEN ACTUATED



LED SPECS	UNITS	RED	GREEN	BLUE
FORWARD CURRENT	mA	20	20	20
FORWARD VOLTAGE @20mA	V	2.1-2.4	3.2-3.9	3.2-3.9
LUMINOUS INTENSITY @20mA	MCD	675	1600	240



TITLE LP110A1TASRGB

A	23964	RELEASE	7/18/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
2:1	7/12/2019	MW	B231022	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP110A1TASRGB](#)