









NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 12mA; SPST
5. CONTACT MATERIAL: GOLD
6. CONTACT RESISTANCE: 50 Milli-OHM MAX.
7. INSULATION RESISTANCE: 500VDC, 100 Mega-OHM MIN.
- ▲ 8. OPERATING FORCE: 150 $\pm$ 100GF
9. OPERATING LIFE: 200,000 CYCLES
10. OPERATING TEMP: -20°C TO +70°C
- ▲ 11. LED COLORS: RED, YELLOW
12. TRAVEL: 2.20mm $\pm$ 0.20
13. 2002/95/EC (ROHS) COMPLIANT
14. ▲ DENOTES CRITICAL PARAMETER.



▲ LED SPECS	UNITS	RED	YELLOW
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE @20mA	VDC	1.95-2.20	1.95-2.20
LUMINOUS INTENSITY @ 10mA	mcd	77	232



E-SWITCH®



TITLE LP60A1ASRY

A	19231	RELEASE FOR PRODUCTION	8/12/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2=1

DATE 8/12/2010

DR BLR

DWG B220007

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP60A1ASRY](#)