









PANEL CUTOUT




SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	OFF
5-6, 3-2	N/A	OPEN



NOTE:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- CONTACT RATINGS:
ANSI/UL 61058-1
16(8)A @ 125/250VAC T55 [cURus] [ENEC15]
- CONTACT RESISTANCE: 20mΩ MAX. @ 50VAC INITIAL
- INSULATION RESISTANCE: 100MΩ MIN. @ 500VDC
- DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
- ELECTRICAL LIFE: 10,000 CYCLES [cURus]
- OPERATING TEMPERATURE: 0°C to 55°C [cURus]
- INGRESS PROTECTION: IP67
- ILLUMINATION VOLTAGE: 125V
- ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-102208	UPDATED CIRCUIT SCHEMATIC	09/01/23	JS	TITLE RB541A1100-16				100125271
A	ECO-102141	RELEASE	08/07/23	JS					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV
					1:1	8/1/2023	JS	14-RB541A110016	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RB541A1100-16](#)