





COMPLEMENT CODE

B	C	1	2	4	8
0	●	●	●	●	0
1	●	●	●	●	1
2	●	●	●	●	2
3	●	●	●	●	3
4	●	●	●	●	4
5	●	●	●	●	5
6	●	●	●	●	6
7	●	●	●	●	7
8	●	●	●	●	8
9	●	●	●	●	9
10	●	●	●	●	A
11	●	●	●	●	B
12	●	●	●	●	C
13	●	●	●	●	D
14	●	●	●	●	E
15	●	●	●	●	F

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
3. TERMINAL NUMBERS FOR REFERENCE ONLY
4. OPERATING FORCE: 120gf/cm $\pm$ 30gf
- ▲ 5. CONTACT RATING: 100mA, 42V DC (SWITCHING)
400mA 42V DC (NON-SWITCHING)
6. CONTACT RESISTANCE: 80m Ω MAX.
7. INSULATION RESISTANCE: 100M Ω MIN @ 250VDC
8. DIELECTRIC STRENGTH: 250VAC 1 MIN.
9. LIFE: 25,000 STEPS
10. OPERATING TEMPERATURE: -60°C TO 125°C
11. PACKAGING: 70 PCS TUBE
12. IP RATING: IP67
13. ▲ DENOTES CRITICAL PARAMETER
14. 2002/95/EC (ROHS) COMPLIANT



C	19878	CORRECT TERMINAL CALL-OUTS	04/26/11	BMA
B	19865	ADD BARS TO COMPLEMENT CODE	04/21/11	BMA
A	19711	RELEASE TO PRODUCTION	02/24/11	BMA
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE RDMAC16P1T

SCALE 3:1

DATE 2/24/2011

DR BMA

DWG U100003

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RDMAC16P1T](#)