



SWITCH	WIRE
SW1-1	WIRE, 18AWG AWM UL3266, GREEN
SW1-2	WIRE, 18AWG AWM UL3266, PINK
SW1-3	WIRE, 18AWG AWM UL3266, YELLOW





RECOMMENDED PANEL CUT OUT

▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
(ON)	OFF	(ON)
2-3	OPEN	1-2

() = DENOTES MOMENTARY

NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: X.X = ± 0.5
X.XX = ± 0.25
- TERM. NOS. FOR REFERENCE ONLY
- ELECTRICAL LIFE: 6,000 CYCLES
- OPERATING TEMP: 0°C to 85°C
- CONTACT RESISTANCE: 50mΩ MAX. INITIAL
- INSULATION RESISTANCE: 2MΩ AT 500VDC
- DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER
- CONTACT RATING: 20A 125VAC,
15A 277VAC
1.5HP 125/277VAC
- SUPPLIED HARDWARE: 2 HEXNUTS



TITLE ST1WDD10

SCALE 2:3

DATE 10/7/2020

DR MJR

DWG 34-ST1WDD10

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ST1WDD10](#)