






RECOMMENDED PANEL CUT OUT

| ▲ SWITCH FUNCTION | | |
|-------------------|--------|----------|
| POS. 1 | POS. 2 | POS. 3 |
| | | |
| ON | N/A | ON |
| 2-3, 5-6 | N/A | 1-2, 4-5 |

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ±0.5
X.XX = ±0.25
3. TERM. NOS. FOR REFERENCE ONLY
4. ELECTRICAL LIFE: 6,000 CYCLES
5. OPERATING TEMP: 0°C to 85°C
6. CONTACT RESISTANCE: 50mΩ MAX. INITIAL
7. INSULATION RESISTANCE: 2MΩ AT 500VDC
8. DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT RATING: 20A 125VAC,
15A 277VAC
2HP 125/277VAC
- ▲ 11. SUPPLIED HARDWARE: 2 HEXNUTS


 OBJECT ID
000001101

| | | | | |
|-----|--------|----------------------------------|----------|-----|
| C | 24486 | DRAWING UPDATE CAD TO INVENTOR | 9/14/20 | MJR |
| B | 19380 | CORRECTED PANEL CUTOUT AND SPECS | 11/16/10 | CAB |
| REV | PCR NO | DESCRIPTION | DATE | BY |

 THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE ST24GD00

SCALE
2:3DATE
8/5/2009DR
CABDWG
34-ST24GD00REV
C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ST24GD00](#)