





P.C. MOUNTING



CIRCUIT: 2PDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]

2. GENERAL TOLERANCE: X.X=±0.4

X.XX=±0.25

3. TERM. NOS. FOR REFERENCE ONLY.

4. RATING 0.1A @30V DC

▲ 5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE

HOUSING: PBT UL94HB

BASE: PA66 UL94HB

ACTUATOR: POM

CAP: ABS UL94V0

6. CONTACT RESISTANCE: 100 mΩ (INITIAL)

▲ 7. TIMING: NON-SHORTING

8. OPERATING FORCE: 230±50GF

9. TRAVEL: LATCHING

2MM TO LOCK




3MM OVERALL

10. ELECTRICAL LIFE: 10000 CYCLES


11. OPERATING TEMP: -20°C TO +70°C

12. 2002/95/EC (ROHS) COMPLIANT

13. ▲ DENOTES CRITICAL PARAMETER.

PBH2UEEKZXNAGX
(Q960007)1RBLK
(Q800306)

ISOMETRIC



F	15942	MOVE KZX 0.45MM CLOSER TO SWITCH	4/4/06	BK
E	15681	CHAGNES NOTED	1/16/06	PH
D	15336	ADDED ROHS NOTE, EDIT PC MOUNT.	9/27/05	PH
C	15260	REVISED CAP DESCRIPTION, NOTE 5	9/8/05	PH
B	15213	CHANGES TO NOTE 9	8/29/05	PH
A	15108	RELEASED FOR PRODUCTION	8/4/05	BK
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED**E-SWITCH®**

TITLE PBH2UEEKZXNAG1RBLK

SCALE 2.5:1

DATE 08/04/05

DR BK

DWG XQ0010P

REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PBH2UEEKZXNAG1RBLK](#)