







NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 36 VDC
6. ELECTRIC LIFE: 200,000 CYCLES
7. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
8. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
9. OPERATING TEMP.: -20°C to 70°C
10. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 11. LAMP VOLTAGE: RED 20mA 2.0V typ., BLUE 20mA 3.1V typ.
12. TRAVEL: 1.80mm
13. ACTUATION FORCE: 4.5 $\pm$ 1.5 N
14. MOUNTING NUT TORQUE: 1-3 Nm
15. INGRESS PROTECTION: IP67
16. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-101694	print update	03/06/23	MW	TITLE SV8F23SS-6H1				000025996
					SCALE	DATE	DR	DWG	REV
					1:1	11/5/2019	MJR	T880001	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[SV8F23SS-6H1](#)