



CIRCUIT DIAGRAM



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. TERM: NOS. FOR REFERENCE ONLY.
4. RATING 0.1A @30V DC

▲ 5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE

HOUSING: PBT UL94HB

BASE: PA66 UL94HB

ACTUATOR: POM

6. CONTACT RESISTANCE: 100 MILLI-OHM (INITIAL)

7. TIMING: NON-SHORTING

8. OPERATING FORCE: 280 ± 50 GF

9. TRAVEL: MOMENTARY

2MM TO MAKE

3MM OVERALL

10. ELECTRICAL LIFE: 10000 CYCLES

11. OPERATING TEMP: -20°C TO +70°C

12. $\blacktriangle$ DENOTES CRITICAL PARAMETER.

13. 2002/95/EC (ROHS) COMPLIANCE



TITLE PBH4UOANAG1RRRED

B	19671	UPDATE CIRCUIT DIAGRAM	2/10/11	BGL
A	17962	RELEASED FOR PRODUCTION	2/19/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PBH4UOANAG1RRED](#)