


P.C. MOUNTING



CIRCUIT DIAGRAM

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING 0.1A @30V DC

▲ 5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE
HOUSING: PBT UL94HB
BASE: PA66 UL94HB
ACTUATOR: POM

6. CONTACT RESISTANCE: 100 MILLI-OHM (INITIAL)

▲ 7. TIMING: NON-SHORTING

8. OPERATING FORCE: 280 ± 50 GF
9. TRAVEL: MOMENTARY


- 3MM OVERALL

10. ELECTRICAL LIFE: 10000 CYCLES


11. OPERATING TEMP: -20°C TO +70°C

12. ▲ DENOTES CRITICAL PARAMETER.

13. 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



F	19671	UPDATE CIRCUIT DIAGRAM	2/10/11	BGL
E	15676	ADD ROHS NOTE	1/12/06	PH
D	15669	EDIT PC MOUNT DIM	1/9/06	PH
C	14893	CHANGED NOTES AND DIMMENSIONS	5/3/05	JB
B	14790	ADD MATERIALS TO NOTES	3/29/05	AR
A	14691	RELEASED FOR PRODUCTION	2/14/05	AR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE PBH4UOANAGX

SCALE 2:1

DATE 2/2/2005

DR	
AR	

DWG Q960003

REV
F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PBH4UOANAGX](#)