


PANEL CUTOUT
MAX. PANEL THICKNESS
14.0mm [.55]



4 ○ ○ 5
RED (FORWARD)
(+) ○ (-)
RED (REVERSE)

▲ DPDT ON-(ON)
CONTACT CONFIGURATION


SWITCH FUNCTION

POS. 1	POS. 2
ON	(ON)
1-3, 4-6	1-2, 4-5




(ON) = MOMENTARY

NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 48VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 M Ω MIN.
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 55°C
- ▲ DENOTES CRITICAL PARAMETER.
- HARDWARE SUPPLIED: O-RING AND HEXNUT
- INGRESS RATING: IP40
- LAMP VOLTAGE: 24V



1.50 [.06 in]
▲ BODY POLISHED STAINLESS STEEL



E	23622	update +/- Terminals	2/25/19	MW
D	23362	UPDATED RATING TO 2A 48VDC	5/14/18	MJR
C	22885	UPDATED RATING TO 1A 24VDC	6/19/17	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE PV3F2H0SS-315

SCALE 3:2	DATE 7/28/2015	DR MW	DWG 52-PV3F2H0SS315	REV E
--------------	-------------------	----------	------------------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV3F2H0SS-315](#)