




P.C.B. MOUNTING

▲ ACTUATOR
COLOR: RED

▲ CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 50mA @ 12VDC
5. TRAVEL: 0.30 ± 0.15 mm
- ▲ 6. OPERATING FORCE: 260 ± 50 mm
7. CONTACT RESISTANCE: $100\text{m}\Omega$ MAX.
8. ELECTRICAL LIFE: 100,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-102067	PRINT UPDATE	08/11/23	JS	TITLE TL1100AF260Q				000017214
					SCALE	DATE	DR	DWG	REV
					3:1	10/15/2012	rc	P001112	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL1100AF260Q](#)