









P.C.B. LAYOUT



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 260 ± 50 gms
6. TRAVEL: $0.25 \pm .1$ mm
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
9. CONTACT MATERIAL: SILVER
10. 2002/95/EC (ROHS) COMPLIANT
- ▲ 11. PACKAGING: TAPE and REEL (qty 500 per Reel)
12. ▲ DENOTES CRITICAL PARAMETER



▲ ALL (4) TERMINALS
COPLANAR WITHIN .10(.004")

B	22478	update to show 9.50 dimension	9/1/16	MW
A	22365	Release for Production	6/22/2016	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL3301BF260QG (Tape and Reel)

SCALE 4:1

DATE 6/22/2016

DR MW

DWG P010695

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL3301BF260QG](#)