




SERIES TL 3330 SWITCHES

TACT SWITCHES SMT - RIGHT ANGLE



FEATURES & BENEFITS

- ▶ Multiple gram force options
- ▶ Small profile works great for many consumer electronic applications

APPLICATIONS/MARKETS

- ▶ Telecommunications
- ▶ Consumer Electronics
- ▶ Audio/visual
- ▶ Medical
- ▶ Testing/instrumentation
- ▶ Computer/servers/peripherals

SPECIFICATIONS

Contact Rating:	50mA @ 12 VDC
Life Expectancy:	50,000 cycles-F130 30,000 cycles-F260
Contact Resistance:	100mΩ
Insulation Resistance:	100MΩ
Dielectric Strength:	250 VAC
Actuation Force:	130± 40 gf, 260± 50 gf
Operating Temperature:	-30°C to 70°C
Travel:	0.25mm ± 0.15mm

MATERIALS

Actuator:	Nylon
Base:	Nylon
Cover:	Tin Plate
Terminals:	Copper alloy, plated



HOW TO ORDER

SERIES	MODEL NO.	ACTUATOR ("L" Dimension)	OPERATING FORCE	CONTACT MATERIAL	TERMINATION
TL	3330	A = 3.50mm	F130 F260	Q = Silver	G = Gull Wing





Example Ordering Number


TL-3330-A-F260-Q-G

Specifications subject to change without notice.

TL 3330



P.C. MOUNTING



SCHEMATIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[TL3330AF130QG](#) [TL3330AF260QG](#)