


CAP OPTIONS	TOGGLE SWITCHES	TACTILE SWITCHES	SLIDE SWITCHES	ROTARY SWITCHES	ROCKER SWITCHES	PUSHBUTTON SWITCHES	NAVIGATION SWITCHES	KEYLOCK SWITCHES	DIP SWITCHES	DETECTOR SWITCHES	ANTI-VANDAL SWITCHES
----------------	--------------------	---------------------	-------------------	--------------------	--------------------	------------------------	------------------------	---------------------	-----------------	----------------------	-------------------------



RoHS

FEATURES & BENEFITS

- Up to 5,000,000 cycle life expectancy
- Tape and Reel packaging
- IP67 ratings
- Multiple force options

PART NUMBER CONFIGURATOR

Series	Circuit	Actuator	Force	Plating	Termination
 TL	 6150	 A - 3.50 B - 5.20	 F160 - 160 gf - Brown F200 - 200 gf - Red F350 - 350 gf - Orange	 Q - Silver	 G - Gull Wing J - J Lead

Specifications subject to change without notice 2.9.2021






E♦SWITCH®

800.867.2717



1

TL6150 SERIES TACT SWITCH

BODY DIMENSIONS GULL WING






ACTUATOR	"X"	"Y"
A	3.50	2.90
B	5.20	2.70





TL6150 SERIES TACT SWITCH

BODY DIMENSIONS J LEAD



ACTUATOR	"X"	"Y"
A	3.50	2.90
B	5.20	2.70





E-SWITCH®

www.e-switch.com

800.867.2717

TL6150 SERIES TACT SWITCH

BODY DIMENSIONS TAPE AND REEL



E-SWITCH®

www.e-switch.com

800.867.2717

4

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS


RECOMMENDED SOLDER PROCESS

Most contamination problems can be prevented by exercising care during the cleaning and soldering process. Care should be taken not to immerse or spray unsealed switches during flux removal. Contact E-Switch for specific soldering recommendations and specifications not shown. Generalized soldering procedures are outlined below.

“TYPICAL” SMT REFLOW (Pb and Pb-Free)

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average Ramp-Up Rate (T_{smax} to T_p)	3 °C/second max.	3 °C/second max.
Preheat -Temperature Min (T_{smin}) -Temperature Max (T_{smax}) -Time (t_{smin} to t_{smax})	100 °C 150 °C 60-120 seconds	150 °C 200 °C 60-180 seconds
Time Maintained above: -Temperature (T_L) -Time (t_L)	183 °C 60-150 seconds	217 °C 60-150 seconds
Time within 5 °C of actual Peak Temperature (t_p)	10-30 seconds	20-40 seconds
Ramp-Down Rate	6 °C/second max.	6 °C/second max.
Time 25 °C to Peak Temperature	6 minutes max.	8 minutes max.

Note 1: All temperatures refer to topside of the package, measured on the package surface.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[TL6150AF160QG](#) [TL6150AF160QJ](#) [TL6150AF200QG](#) [TL6150AF350QG](#) [TL6150BF160QG](#) [TL6150BF200QG](#)
[TL6150AF350QJ](#) [TL6150BF160QJ](#) [TL6150AF200QJ](#)