



PVA6 SERIES ANTI-VANDAL SWITCH



APPLICATIONS / MARKETS



RoHS

SPECIFICATIONS

Electrical Rating: 2A, 36VDC
Mechanical Life: 1,000,000 Cycles (PVA6L 100,000 Cycles)
Electrical Life: 200,000 Cycles (PVA6L 100,000 Cycles)
Contact Resistance: 50mΩ Max. Initial
Insulation Resistance: 1,000 MΩ @ 500VDC
Dielectric Strength: 2,000V
Operating/Storage Temperature: -20°C to 70°C
Travel: 2.0mm (PVA6L 2.3mm)
Moisture Protection: IP67
Contact Arrangement: SPST
Actuation Force: 460 gf
Panel Thickness: 1-8mm (PVA6L 1-6mm)
Max Hex Nut Torque: 11.5 kgf/cm
Contact Material: Silver (PVA6L Coin Silver, Gold Flash Plated)

FEATURES & BENEFITS

PVA6

- 16mm diameter panel cutout
- Solder lug or wire leads (500 mm long) termination
- Ring or power symbol / ring illumination options
- Multiple actuator options
- IP67 rated, Off-(On), SPST
- Multiple LED colors available

PVA6L - Latching Version

- 16mm diameter panel cutout
- Solder lug or wire leads (500 mm long) termination
- Ring or power symbol / ring illumination options
- IP67 rated, Off-On Latching, SPST
- Multiple LED colors available

PART NUMBER CONFIGURATOR

Series Options	Bezel Shape	Button Style	Termination	Circuit Function	Housing Material	LED Color Options	LED Voltage
PVA6	R - Rounded	E - Ring Illumination P - Power Symbol/ Ring Illumination	2 - Solder Lug W - Wire Leads 500mm long	4 - SPST Off - (On)* Momentary	1 - Black Anodized 2 - Clear Anodized	0 - White 1 - Red 3 - Green 4 - Blue 5 - Yellow G - Red/Green bi-color	1 - Base Voltage[†]
PVA6	H - High Flat	E - Ring Illumination	2 - Solder Lug W - Wire Leads 500mm long	4 - SPST Off - (On)* Momentary	S - Stainless Steel	0 - White 1 - Red 3 - Green 4 - Blue 5 - Yellow G - Red/Green bi-color	1 - Base Voltage [†]
PVA6	F - Flat	E - Ring Illumination P - Power Symbol/ Ring Illumination	2 - Solder Lug W - Wire Leads 500mm long	4 - SPST Off - (On)* Momentary	S - Stainless Steel	0 - White 1 - Red 3 - Green 4 - Blue 5 - Yellow G - Red/Green bi-color	1 - Base Voltage [†]
PVA6L	R - Rounded	E - Ring Illumination P - Power Symbol/ Ring Illumination	2 - Solder Lug W - Wire Leads 500mm long	1 - SPST Off - On Latching	1 - Black Anodized 2 - Clear Anodized	0 - White 1 - Red 3 - Green 4 - Blue 5 - Yellow G - Red - Off Position/ Green - On Position bi-color	1 - Base Voltage ^{††}

NOTES:
 *() denotes function is momentary
[†]PVA6 Base voltage on LEDs: 1.7V - 2.5V @ 20mA; 2.0V Typ @ 20mA for Red and Yellow LED colors
 2.8V - 3.7V @ 20mA; 3.1V Typ @ 20mA for Blue, Green, and White LED colors
^{††}PVA6L Base voltage on LEDs: 3V @ 20mA for all LED colors

Specifications subject to change without notice 4.26.2022



E-SWITCH®




www.e-switch.com

800.867.2717




1

PVA6 SERIES ANTI-VANDAL SWITCH



BODY DIMENSIONS PVA6 ROUNDED BEZEL



RING ILLUMINATED






POWER SYMBOL/RING ILLUMINATED





PVA6 SERIES ANTI-VANDAL SWITCH



BODY DIMENSIONS PVA6 HIGH FLAT BEZEL



RING ILLUMINATED



WIRE LEADS



E-SWITCH®




www.e-switch.com

800.867.2717




3

PVA6 SERIES ANTI-VANDAL SWITCH


BODY DIMENSIONS PVA6 FLAT BEZEL




RING ILLUMINATED



POWER SYMBOL/RING ILLUMINATED



SCHEMATIC



PVA6 FLAT PANEL CUTOUT



E-SWITCH®

www.e-switch.com

800.867.2717

4

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

ANTI-VANDAL SWITCHES

DETECTOR SWITCHES



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PVA6LRE21231](#) [PVA6LRE21141](#) [PVA6LRE21241](#) [PVA6LRE21111](#) [PVA6LRE212G1](#) [PVA6LRE211G1](#)
[PVA6LRE21131](#) [PVA6LRE21211](#) [PVA6RPW41G1](#) [PVA6RPW41K1](#) [PVA6REW4111](#) [PVA6LRPW1141](#)
[PVA6RPW4141](#) [PVA6HE24SG1](#) [PVA6HE24S11](#) [PVA6RE24111](#) [PVA6RP24211](#) [PVA6RP24101](#) [PVA6RP24231](#)
[PVA6FE24SG1](#) [PVA6RP24131](#) [PVA6REW41G1](#) [PVA6FPW4S41](#) [PVA6RE24241](#) [PVA6FP24S41](#) [PVA6RP24141](#)
[PVA6FE24S31](#) [PVA6RE24101](#) [PVA6FP24S01](#) [PVA6RP24241](#) [PVA6REW4141](#) [PVA6RE24141](#) [PVA6RE241G1](#)
[PVA6FE24S41](#) [PVA6FE24S51](#) [PVA6FP24S31](#) [PVA6FPW4SG1](#) [PVA6HEW4SG1](#) [PVA6LRP21241](#) [PVA6RPW42G1](#)
[PVA6FEW4S41](#) [PVA6LRPW12G1](#) [PVA6RPW4241](#) [PVA6HEW4S41](#) [PVA6LRP211G1](#) [PVA6FP24SG1](#)
[PVA6HE24S31](#) [PVA6RP241G1](#) [PVA6RP24201](#) [PVA6REW41K1](#) [PVA6LRP21141](#) [PVA6LRPW1111](#)
[PVA6LRPW1131](#) [PVA6LRPW11G1](#) [PVA6LRP21111](#) [PVA6FEW4S11](#) [PVA6REW4131](#) [PVA6REW4231](#)
[PVA6RPW4101](#) [PVA6RPW4131](#) [PVA6LRPW1241](#) [PVA6LREW1241](#) [PVA6RE24131](#) [PVA6RE24231](#)
[PVA6LREW1101](#) [PVA6FE24S13V](#) [PVA6FP24S13V](#) [PVA6HE24S13V](#) [PVA6RE24113V](#) [PVA6LREW1211](#)
[PVA6HE24S41](#) [PVA6LRP21231](#) [PVA6RE242G1](#) [PVA6LRE21101](#) [PVA6LRPW1101](#) [PVA6LREW11G1](#)
[PVA6LRP21101](#) [PVA6LREW1131](#) [PVA6LREW12G1](#) [PVA6FEM4S11](#) [PVA6RPM4101](#)