



PANEL CUTOUT
MAX. PANEL THICKNESS
10.0mm [.43]






SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	ON	ON
1-3, 4-5	1-3, 4-6	1-2, 4-6



▲ DP3T ON-ON-ON
CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN mm [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 M Ω MIN.
8. DIELECTRIC STRENGTH: 1,500 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. INGRESS PROTECTION: IP40
- ▲ 13. HARDWARE SUPPLIED: KEY, O-RING, AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-101460	REMOVE + AND - LED STAMP	11/29/22	MR					100122492
A	ECO-101165	NEW RELEASE	09/06/22	MR	TITLE PVK4K22C0SS				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1:1	DATE 9/6/2022	DR MJR	DWG 52-PVK4K22C0SS	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PVK4K22C0SS](#)