

ULV8 SERIES ANTI-VANDAL SWITCH

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS




Commercial Appliances



Security Devices



Industrial Controls



Kiosks



Electrical Housewares



Medical Equipment



RoHS

SPECIFICATIONS

Electrical Rating: 3A, 125/250VAC
Mechanical Life: 1,000,000 cycles (momentary); 500,000 cycles (latching)
Electrical Life: 50,000 Cycles
Contact Resistance: 50mΩ Max. at 1A 12VDC
Insulation Resistance: ,000MΩ min. @ 500 VDC
Dielectric Strength: 2,000V RMS at sea level
Operating/Storage Temperature: -20°C to 55°C
Travel: 3.2mm
Moisture Protection: IP67
Contact Arrangement: SPDT or DPDT
Actuation Force: SPDT: 2.5N; DPDT: 3.5N,
 Molded Back: SPDT & DPDT: 5.5N
Panel Thickness: 1-10mm
Hex Nut Torque: 5-14Nm
Mechanical Impact Protection: IK08 (Stainless)
Agency Approvals: cURus

FEATURES & BENEFITS

- 25mm diameter panel cutout
- Ring or Ring/Power symbol illumination
- Multiple switch functions available
- Multiple illumination voltage options
- IP67 rated
- SPDT or DPDT
- UL Certified
- Soldered wire leads (300mm long) optional
- Detachable socket w/ wire leads (500mm long) optional
- Molded back w/ wire leads (500mm long) optional

PART NUMBER CONFIGURATOR

Series	Actuator	Terminal	Function	Body Finish	Actuator Finish	Contact Material	Lens Style	LED Color	Illumination Voltage	Graphic Options
ULV8	F - Flat	2 - Solder Lug	3 - 1P ON-ON	S - Stainless Steel	S - Stainless Steel	None - Silver	3 - Ring	0 - White	1 - 3V	L17 - Bluetooth
		W - Wire Leads	B - 1P ON-(ON)*	Steel	1 - Black	G - Gold	Illumination, movable with actuator	1 - Red	3 - 6V	L18 - Wifi
		300mm long	G - 2P ON-ON	1 - Black	Anodized		6 - Ring / Power	2 - Orange	4 - 12V	L20 - START
		P - Detachable	H - 2P ON-(ON)*	Anodized	L - Silver for Graphic		Symbol Illumination, movable with actuator	3 - Green	5 - 24V	L21 - OFF
		Socket w/ Wire Leads 500mm long					Stainless Steel only	4 - Blue	6 - 110V	L22 - ON
		M - Molded Back w/ Wire Leads 500mm long					L - Graphic Illumination (Only Available with L Actuator Finish)	5 - Yellow	7 - 220V	L35 - STOP
								F - Red / Orange		
								G - Red / Green		
								H - Red / Blue		
								J - Red / Yellow		
								K - Orange / Green		
								N - Blue / Green		
								P - Green / Yellow		
								Q - Blue / Yellow		

NOTES:

*() denotes function is momentary

Specifications subject to change without notice 12.16.2021



E-SWITCH®






www.e-switch.com

800.867.2717

1



ULV8 SERIES ANTI-VANDAL SWITCH

BODY DIMENSIONS - SPDT



HOUSING WITH FLATS (SPDT OR DPDT) USED ON SWITCHES WITH RING/POWER SYMBOL OR OTHER GRAPHICS (SPDT SHOWN)

SPDT SWITCH DIMENSIONS



E-SWITCH®

www.e-switch.com

800.867.2717

2

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES



TACTILE
SWITCHES

TOGGLE
SWITCHES



CAP
OPTIONS

ULV8 SERIES ANTI-VANDAL SWITCH

BODY DIMENSIONS - DPDT



DPDT SWITCH DIMENSIONS



E-SWITCH®



www.e-switch.com

800.867.2717


3

ULV8 SERIES ANTI-VANDAL SWITCH


SCHEMATICS



ACUATOR OPTIONS



RING ILLUMINATED



RING / POWER SYMBOL ILLUMINATED



E-SWITCH®

www.e-switch.com

800.867.2717

4

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS


ULV8 SERIES ANTI-VANDAL SWITCH

WIRE OPTIONS

W - Wire Leads
300mm long

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-2	WIRE, 24AWG AWM UL1015, PURPLE	300.0 [11.8 in]
SW1-3	WIRE, 24AWG AWM UL1015, GREEN	300.0 [11.8 in]
SW1-4	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-5	WIRE, 24AWG AWM UL1015, ORANGE	300.0 [11.8 in]
SW1-6	WIRE, 24AWG AWM UL1015, YELLOW	300.0 [11.8 in]
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]
SW1- (+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]


** WIRE LEADS PROVIDED ARE DEPENDENT ON THE FUNCTION SELECTED **



M - Molded Back w/ Wire Leads
500mm long

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 18 AWG AWM UL3385, YELLOW	500.0 [19.7 in]
SW1-2	WIRE, 18 AWG AWM UL3385, PURPLE	500.0 [19.7 in]
SW1-3	WIRE, 18 AWG AWM UL3385, GREEN	500.0 [19.7 in]
SW1-4	WIRE, 18 AWG AWM UL3385, YELLOW	500.0 [19.7 in]
SW1-5	WIRE, 18 AWG AWM UL3385, PURPLE	500.0 [19.7 in]
SW1-6	WIRE, 18 AWG AWM UL3385, GREEN	500.0 [19.7 in]
SW1- (-)	WIRE, 18 AWG AWM UL3385, BLACK	500.0 [19.7 in]
SW1- (+)	WIRE, 18 AWG AWM UL3385, RED	500.0 [19.7 in]

** WIRE LEADS PROVIDED ARE DEPENDENT ON THE FUNCTION SELECTED **



E-SWITCH®

www.e-switch.com

800.867.2717

5


ULV8 SERIES ANTI-VANDAL SWITCH

WIRE OPTIONS

P - Detachable Socket
w/ Wire Leads
500mm long

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 18 AWG AWM UL3385, GREEN	500.0 [19.7 in]
SW1-2	WIRE, 18 AWG AWM UL3385, PURPLE	500.0 [19.7 in]
SW1-3	WIRE, 18 AWG AWM UL3385, YELLOW	500.0 [19.7 in]
SW1-4	WIRE, 18 AWG AWM UL3385, GREEN	500.0 [19.7 in]
SW1-5	WIRE, 18 AWG AWM UL3385, PURPLE	500.0 [19.7 in]
SW1-6	WIRE, 18 AWG AWM UL3385, YELLOW	500.0 [19.7 in]
SW1- (-)	WIRE, 18 AWG AWM UL3385, BLACK	500.0 [19.7 in]
SW1- (+)	WIRE, 18 AWG AWM UL3385, RED	500.0 [19.7 in]

** WIRE LEADS PROVIDED ARE DEPENDENT ON THE FUNCTION SELECTED **



E-SWITCH®

www.e-switch.com

800.867.2717

6

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES



TOGGLE
SWITCHES

CAP
OPTIONS


ULV8 SERIES ANTI-VANDAL SWITCH

GRAPHIC OPTIONS


** REFER TO BODY DIMENSION PAGES 2 & 3 FOR GRAPHIC ORIENTATION **



L02




L03



L04




L05




L06




L07




L08




L09




L10




L11




L12



L13




L14



L15



L16




L17



L18




L19




L20



L21



L22



L23



L24



E-SWITCH®

www.e-switch.com












800.867.2717

7

ULV8 SERIES ANTI-VANDAL SWITCH

GRAPHIC OPTIONS (CONT.)

** REFER TO BODY DIMENSION PAGES 2 & 3 FOR GRAPHIC ORIENTATION **



ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS



E-SWITCH®

www.e-switch.com

800.867.2717

8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[ULV8F2GSS341](#) [ULV8F2HSS341](#) [ULV8F2BSS331](#) [ULV8F23SS311](#) [ULV8F23SS305](#) [ULV8FWHSS341](#)
[ULV8FWGSS341](#) [ULV8FWBSS331](#) [ULV8FWBSS344](#) [ULV8F2GSS3G5](#) [ULV8F2GSS335](#) [ULV8F2GSS315](#)
[ULV8F2GSS343](#) [ULV8F2GSS351](#) [ULV8F23SS635](#) [ULV8F2B11G331](#) [ULV8F2B11G351](#) [ULV8F2311333](#)
[ULV8F2311334](#) [ULV8F23SS334](#) [ULV8F2B113G1](#) [ULV8F2BSS311](#) [ULV8F2BSS341](#) [ULV8F23SS351](#)
[ULV8F2311335](#) [ULV8F23113G1](#) [ULV8F2B11304](#) [ULV8F2B11335](#) [ULV8F23SSG334](#) [ULV8F23SS3H5](#)
[ULV8F2BSS343](#) [ULV8F2BSS334](#) [ULV8F2BSS344](#) [ULV8F2BSS351](#) [ULV8F2BSS3G4](#) [ULV8F2BSSG301](#)
[ULV8F2BSSG305](#) [ULV8F2BSSG3G5](#) [ULV8F2BSSG3H5](#) [ULV8F2H113H5](#) [ULV8F2HSS305](#) [ULV8F2HSS315](#)
[ULV8F2HSS335](#) [ULV8F2HSS3G5](#) [ULV8F23SS333](#) [ULV8F2B11315](#) [ULV8F2BSS305](#) [ULV8F2BSS3G1](#)
[ULV8F2BSS3P1](#) [ULV8F2G11343](#) [ULV8F2HSS3P5](#) [ULV8F23SS634](#) [ULV8F2HSS3F5](#) [ULV8F2HSS3H5](#)
[ULV8F2HSS3J5](#) [ULV8F2B11301](#) [ULV8F2BSS301](#) [ULV8F2BSS304](#) [ULV8FW3SS311](#) [ULV8FM3SS311](#)
[ULV8FMBSS311](#) [ULV8FPGSS341](#) [ULV8FMBSS331](#) [ULV8FMBSS344](#) [ULV8FMGSS341](#) [ULV8FMHSS341](#)
[ULV8FP3SS311](#) [ULV8FPBSS344](#) [ULV8F2HSS344](#) [ULV8F2HSS3G4](#) [ULV8FM3SS305](#) [ULV8FM3SS315](#)
[ULV8FPBSS331](#) [ULV8FPBSS341](#) [ULV8F2BSLL15L35](#) [ULV8F2BSLL34L20](#) [ULV8FPHSS3G5](#) [ULV8F2BSS3P5](#)
[ULV8FWGSS335](#) [ULV8F23SLL41L17](#) [ULV8F23SS6H5](#) [ULV8F2GSLL43L18](#) [ULV8F2HSLL16L21](#)
[ULV8F2HSLL37L22](#) [ULV8FPHSS3H5](#) [ULV8F23SS356](#)