



RECOMMENDED PANEL CUT-OUT

PANEL THICKNESS	X
1.0 - 1.5	37.3 $^{+0.0}_{-0.1}$
2.5 - 3.0	37.5 $^{+0.0}_{-0.1}$
3.5 - 4.5	37.7 $^{+0.0}_{-0.1}$







▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
(ON)	OFF	(ON)
1-2; 4-5	OFF	2-3; 5-6

() = MOMENTARY FUNCTION

CIRCUIT: DPDT
(ON) - OFF - (ON)

() = MOMENTARY FUNCTION



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REF. ONLY
- ▲ 4. RATING: 16A @ 30 VDC, 50/60 Hz, μ T55
UL LISTED
5. ELECTRICAL LIFE: 10,000 CYCLES
6. MECHANICAL LIFE: 30,000 CYCLES
7. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
8. DIELECTRIC STRENGTH: >1,500V AC 1MIN
9. INSULATION RESISTANCE: >100 MOHMS @ 500VDC
10. OPERATING TEMP: 0°C to 55°C
- ▲ 11. LED VOLTAGE: N/A
12. ▲ DENOTES CRITICAL PARAMETER.



E-SWITCH®

A	24765	Release	3/1/21	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE R726FA1-SXXXNBDNNX

SCALE
1:1DATE
3/2/2021DR
MWDWG
C700045REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R726FA1-SXXXNBDNNX](#)