



RECOMMENDED PANEL CUT-OUT

| PANEL THICKNESS | X |
|-----------------|-----------------------|
| 1.0 - 1.5 | 37.3 $^{+0.0}_{-0.1}$ |
| 2.5 - 3.0 | 37.5 $^{+0.0}_{-0.1}$ |
| 3.5 - 4.5 | 37.7 $^{+0.0}_{-0.1}$ |



| ▲ SWITCH FUNCTION | | |
|-------------------|--------|----------|
| POS. 1 | POS. 2 | POS. 3 |
| | | |
| (ON) | OFF | (ON) |
| 1-2; 4-5 | OFF | 2-3; 5-6 |

() = MOMENTARY FUNCTION






CIRCUIT: DPDT
(ON) - OFF - (ON)

() = MOMENTARY FUNCTION

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERM. NUMBERS FOR REF. ONLY
- ▲ 4. RATING: 16A @ 30 VDC, 50/60 Hz, μ T55
UL LISTED
- ELECTRICAL LIFE: 10,000 CYCLES
- MECHANICAL LIFE: 30,000 CYCLES
- CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
- DIELECTRIC STRENGTH: >1,500V AC 1MIN
- INSULATION RESISTANCE: >100 MOHMS @ 500VDC
- OPERATING TEMP: 0°C to 55°C
- ▲ 11. LED VOLTAGE: N/A
- ▲ 12. ▲ DENOTES CRITICAL PARAMETER.



TITLE R726FB1-SXXXNBDNNX

SCALE 1:1

DATE 3/2/2021

DR MW

DWG C700046

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R726FB1-SXXXNBDNNX](#)