


RB2 SERIES ROCKER SWITCH


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS



Commercial Appliances



Industrial Controls




Floor Care Appliances



Instrumentation



Medical/Dental



Electrical Housewares

RoHS

SPECIFICATIONS

Electrical Rating:

Option C: 16A 125VAC T85 [cURus]
7.5A 250VAC T85 [cURus]
16(4)A 250V~ 1E4 T125/55 [ENEC]

Option D (2 Position Functions):

20A 125VAC T105 [cURus]
16A 250VAC T105 [cURus]
3/4HP 125VAC T105 [cURus]
3/4HP 250VAC T105 [cURus]
20(8)A 250V~ 1E4 T125/55 [VDE, ENEC]
10(2)A 250V~ 5E4 T85/55 [VDE, ENEC]
16(4)A 250V~ 1E4 T85/55 [VDE, ENEC]

Option E (3 Position Functions):

16A 125VAC T65 [cURus]
16A 250VAC T65 [cURus]

Operating Temperature: -20°C to 65°C

Electrical Life: 10,000 Cycles

Contact Resistance: 35mΩ Max. at 50VAC

Insulation Resistance: 100MΩ Min. at 500VDC

Dielectric Strength: 1,500VAC for 1 min.

Ingress Protection: IP54 with optional silicone cap

FEATURES & BENEFITS

- High Quality and Reliable Switch
- Industry Standard 22mm x 30mm Cutout
- Illumination Options
- Marking Options
- Multiple Terminal and Actuator Options
- Front Panel Mount Applications
- Optional Cap for Dust and Water Protection
- 2 Pole Maintained and Momentary Functions

PART NUMBER CONFIGURATOR

Series	Terminal	Function	Rating	Body Color	Actuator Color	Marking Color	Marking Type	Lens Style	Lens Color	Lamp Voltage
RB2	1 - 4.8mm Tab 4 - 6.3mm Tab	2 - Off-On E - Off-(On) G - On-On H - On-(On) 6 - On-Off-On J - On-Off-(On) K - (On)-Off-(On)	C - 16A 125V D - 20A 125V E - 16A 125V	1 - Black 2 - White 3 - Almond 4 - Grey 9 - Red	0 - Full Illumination 1 - Black 2 - White 3 - Almond 4 - Grey 5 - Orange 7 - Blue 8 - Green 9 - Red	0 - None 1 - Black 2 - White 8 - Red	0 - None 1 - I/O Vertical 2 - ON-OFF-ON Vertical 3 - ON-OFF Vertical 4 - ON-OFF Horizontal 9 - I/O/II Horizontal R - I/O Horizontal S - I/O/II Vertical	None - Not Illuminated 1 - Full 2 - Round*	None - Not Illuminated 0 - Clear 1 - Red 2 - Amber 3 - Green 4 - Blue 5 - Yellow	None - Not Illuminated 4 - 12V 5 - 24V 6 - 125V 7 - 250V
Notes: Custom Colors and Markings Available Upon Request () = Denotes Momentary Function * = Only Available with the "C" Rating										

Specifications subject to change without notice 8.14.2018



E-SWITCH®

www.e-switch.com



800.867.2717

1




Body Dimensions

FUNCTION	POS. 1 	POS. 2 	POS. 3 
2	OFF	NONE	ON
E	OFF	NONE	(ON)
G	ON	NONE	ON
H	ON	NONE	(ON)
6	ON	OFF	ON
J	ON	OFF	(ON)
K	(ON)	OFF	(ON)
TERMINAL CLOSURE	2-3, 5-6	OPEN	2-1, 5-4

() = MOMENTARY



2 POLE VERSION
SHOWN WITH C - RATED BODY
TERMINAL - 5 (4.8mm TAB)








RB2 SERIES ROCKER SWITCH

BODY DIMENSIONS

FUNCTION	POS. 3	POS. 2	POS. 1
2	OFF	NONE	ON
E	OFF	NONE	(ON)
G	ON	NONE	ON
H	ON	NONE	(ON)
6	ON	OFF	ON
J	ON	OFF	(ON)
K	(ON)	OFF	(ON)
TERMINAL CLOSURE	2-1, 5-4	OPEN	2-3, 5-6

() = MOMENTARY



E-SWITCH®

www.e-switch.com

800.867.2717




3

ANTI-VANDAL SWITCHES	DETECTOR SWITCHES	DIP SWITCHES	KEYLOCK SWITCHES	NAVIGATION SWITCHES	PUSHBUTTON SWITCHES	ROCKER SWITCHES	ROTARY SWITCHES	SLIDE SWITCHES	SNAP ACTION SWITCHES	TACTILE SWITCHES	TOGGLE SWITCHES	CAP OPTIONS
----------------------	-------------------	--------------	------------------	---------------------	---------------------	-----------------	-----------------	----------------	----------------------	------------------	-----------------	-------------


FUNCTION	POS. 3 	POS. 2 	POS. 1
2	OFF	NONE	ON
E	OFF	NONE	(ON)
G	ON	NONE	ON
H	ON	NONE	(ON)
6	ON	OFF	ON
J	ON	OFF	(ON)
K	(ON)	OFF	(ON)
TERMINAL CLOSURE	2-1, 5-4	OPEN	2-3, 5-6

The diagram shows a rectangular panel cutout. The width is labeled (x) with a dimension line. The height is labeled with two values and tolerances: 22.00 ^{+0.10}/_{-.00} and [.866 ^{+0.004}/_{-.000} in].

PANEL THICKNESS	(x)	TOLERANCE
0.75 - 1.25	30.0	+/- 0.1
1.25 - 2.00	30.2	+/- 0.1
2.00 - 3.00	30.5	+/- 0.1



2 POLE VERSION
SHOWN WITH E - RATED BODY
TERMINAL - 4 (6.3mm TAB)








RB2 SERIES ROCKER SWITCH

BODY DIMENSIONS

FUNCTION	POS. 3	POS. 2	POS. 1
2	OFF	NONE	ON
E	OFF	NONE	(ON)
G	ON	NONE	ON
H	ON	NONE	(ON)
6	ON	OFF	ON
J	ON	OFF	(ON)
K	(ON)	OFF	(ON)
TERMINAL CLOSURE	2-1, 5-4	OPEN	2-3, 5-6

() = MOMENTARY



2 POLE VERSION
SHOWN WITH E - RATED BODY
TERMINAL - 4 (6.3mm TAB)
ACC-F02-1 (SILICONE CAP)



E-SWITCH®

www.e-switch.com


800.867.2717

5


RB2 SERIES ROCKER SWITCH

ILLUMINATION TYPE/ MARKING TYPE


ILLUMINATION TYPE




MARKING TYPE




0 - NONE




1 - I/O
VERTICAL




2 - ON-OFF-ON
VERTICAL




3 - ON-OFF
VERTICAL




4 - ON-OFF
HORIZONTAL



9 - I/O/II
HORIZONTAL



R - I/O
HORIZONTAL



S - I/O/II
VERTICAL



E-SWITCH®

www.e-switch.com

800.867.2717

6

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[RB24GD1100](#) [RB246E1100](#) [RB242D1121](#) [RB242D1000-116](#) [RB24HD1100](#) [RB20001100](#) [RB24001000-114](#)
[RB242C102R-137](#) [RB242D1011-127](#) [RB242D1024-117](#) [RB24GC1100](#) [RB24GC1200](#) [RB2F42C1021-127](#)
[RB245C112S](#) [RB246C1100](#) [RB246C1129](#) [RB246C1219](#) [RB24KC1100](#) [RB2F42C1000-147](#) [RB2F42C1021-117](#)
[RB2F42C1021-147](#) [RB2F42C102R-147](#) [RB241C1100](#) [RB241C1121](#) [RB241C1123](#) [RB242C1000-116](#) [RB242C1000-136](#) [RB242C1011-127](#) [RB242C101R-137](#) [RB242C1021-116](#) [RB242C1021-117](#) [RB242C1021-137](#) [RB242C1100](#)
[RB242C1100-217](#) [RB242D1014-117](#) [RB242D1021-136](#) [RB242D1100](#) [RB243C1100](#) [RB242D1000-125](#)
[RB212C1011-137](#) [RB2F42C1000117/ACC-F02-1](#) [RB24KE1100](#) [RB242D1128/ACC-F02-1](#) [RB242D142R](#)
[RB212C1121](#) [RB242C1100-217/ACC-F02-1](#) [RB242D1011-116/ACC-F04-1](#) [RB24JE1100](#) [RB212C1000-127](#)
[RB242D1800](#) [RB246E112S-ACCF02-1](#) [RB242C1121](#) [RB242D1000-136/ACC-F02-1](#) [RB24GD1100/ACC-F02-1](#)
[RB242D1900](#) [RB242C1021-114](#) [RB212C1011-136](#) [RB24ED1100](#) [RB241D1121/ACC-F02-1](#) [RB245C112S-ACCF02-1](#)
[RB242D1021-117/ACC-F02-1](#) [RB242C1100-216/ACC-F02-1](#) [RB242D1000-125-ACC-F02-1](#) [RB242D1021-137/ACC-F02-1](#) [RB242D1821](#) [RB242D1021-116](#) [RB242D1000-117](#) [RB242C1021-137ACCF021](#) [RB242D1021-146](#)
[RB242D1000-136](#) [RB242C1100-237](#) [RB242C1921/ACC-F02-1](#) [RB242D1021-136/ACC-F02-1](#) [RB246E1100/ACC-F02-1](#) [RB242D1121/ACC-F02-1](#) [RB242D1000-116/ACC-F02-1](#) [RB242D1021-147](#) [RB242D1021-116/ACC-F02-1](#)
[RB212C1000-126](#) [RB246C1100ACCF021](#) [RB2F42C1000-116ACCF021](#) [RB2F42C1000-107ACCF021](#)
[RB24GC1100ACCF021](#)